



Description

The 5100 Series Hall effect portable gaussmeters represent the most recent design from the world leader in magnetic measuring equipment. This new design incorporates the use of digital signal processing technology making it the world's first hand-held gaussmeter to have a digital signal processor (DSP) on board. F.W. Bell's exclusive Dynamic Probe Correction allows measurements from 0 to 30 kG with a basic accuracy of 1%.

Key features include Auto Zero, Min./Max./Peak Hold, Auto Range and Relative Mode. Both models allow the user to select Gauss, Tesla or Ampere/Meter readings. The 5180 features a corrected analog output ($\pm 3V$ FS) and a USB communication port.

The 5100 Series Hand-Held Gaussmeter's built-in software eliminates the need for complex calibration procedures. User prompts on the custom formatted LCD allow fast, simple push button operation. All models come equipped with a detachable transverse probe, zero gauss chamber, instruction manual, hard carrying case, and four AA batteries. Axial, ultra thin transverse and low-field probes are available as options.

Applications for the 5100 Series range from the most sensitive laboratory environment to the most rugged industrial setting. All instruments are CE compliant.

Features

	Model 5170	Model 5180
Probe Included	X	X
Auto Zero	X	X
Min/Max Hold	X	X
True RMS	X	X
Auto Range	X	X
True Peak Hold		X
Relative Mode		X
Outputs (analog)		X
USB Communication Port		X



5100 Series Specifications

Model	5170	5180
Basic DC Accuracy	2%	1.1%
Frequency Bandwidth	DC-20 kHz	DC-30 kHz
Update Rates		
Display	4 readings/sec	4 readings/sec
Analog Output	None	100K samples/sec
Ranges		
Ultra Low Range (low-field probe only)	1 G	1 G
Low Range	200 G	300 G
Mid Range	2 kG	3 kG
High Range	20 kG	30 kG
Resolution		
Ultra Low Range (low-field probe only)	1 mG	1 mG
Low Range	0.1 G	0.1 G
Mid Range	1.0 G	1.0 G
High Range	10 G	10 G
Display	LCD	LCD
Digits	3 1/2	3 2/3
Readings	Gauss, Tesla, Amps/Meter	Gauss, Tesla, Amps/Meter
Analog Output	None	±3V FS
Communication Port	None	USB (1 samples/sec)

General Information

	All Models
Temperature	
Operating	0°C to 50°C
Storage	-25°C to 70°C
Power	4 AA batteries
Size	6.9 in x 3.9 in x 1.44 in.

Probes and Accessories

Model Number	Description
Model 5180 Probes	
HTD18-0604	4" Transverse Probe
STD18-0404	4" Transverse Probe (incl. w/5180)
STD18-0402	2" Transverse Probe
SAD18-1904	4" Axial Probe
SAD18-1902	2" Axial Probe
Model 5170 Probes	
HTH17-0604	4" Transverse Probe
STH17-0404	4" Transverse Probe (incl. w/5170)
STH17-0402	2" Transverse Probe
SAH17-1904	4" Axial Probe
SAH17-1902	2" Axial Probe
Models 5170/5180 Gaussmeter Probes	
STB1X-0201	Ultra Thin Transverse Probe (0.020" thick)
MOS51-3204	Low Field Probe
Models 5170/5180 Gaussmeter Accessories	
YA-111	Zero Gauss Chamber (for axial, transverse and low-field probes)
PSRD-5	AC Adapter, +5VDC Regulated Output, 110VAC Input, Domestic
PSRI-5	AC Adapter, +5VDC Regulated Output, 220VAC Input, Switching, International

Shipping Weight

Domestic 3.5 lbs 1.59 kgs
International 4 lbs 1.82 kgs

Note: Due to continuous process improvement, specifications are subject to change without notice.



SYPRIS
TEST & MEASUREMENT

6120 Hanging Moss Road • Orlando, Florida 32807 • www.fwbell.com
Phone (407) 678-6900 • Fax (407) 677-5765 • Toll Free (800) 778-6117



Rev. date 05/2006

Hall Effect Gaussmeters